



Innovating Radiation Detection Technologies Since 1992

CONTINUOUS AND PULSE X-RAY AND GAMMA RADIATION PERSONAL DOSIMETER

PM1610B PM1610B-01

These electronic personal dosimeters are excellent instruments for personnel, exposed to pulsed X-ray and gamma radiation.

The instruments provide measurement of dose equivalent and dose equivalentrate of continuous and pulsed X-ray and gamma radiation, as well as time of dose accumulation.

Devices have audible, visual and vibration alarms to warn the user when preset dose/dose rate threshold levels are exceeded.

For reading data from dosimeters the special software Personal Dose Tracker is provided. It allows to record and monitor radiation exposure of users of dosimeters.

The device is ready for use immediately after installing the battery.

PM1610B-01 version can be used with different types of wireless readers in compliance with ISO 15693.

Features

- Easy to use
- Measurement of pulse X-ray and gamma radiation with pulse duration 1 ms and up
- Dose rate measurement up to 10 Sv/h (1000°Rem/h) and dose measurement up to 20°Sv (2000 Rem)
- Two independent alarm thresholds for dose and dose rate
- Default settings for dose:
 threshold 1 5 mSv (500 mRem),
 threshold 2 10 mSv (1000 mRem)
- Audible, visual and vibration alarms
- Wide energy range from 20 keV to 10 MeV
- Settings can be controlled (blocked by the user to change) from a PC via USB
- Ability to display measurements in Sv or Rem
- Turning off the alarm by pressing any button
- Shockproof hermetic case
- Light weight and small dimensions













USB RF-ID

Applications

- First responders
- Customs and border patrol
- Medical professionals
- Radiological and Radionuclide isotope laboratories
- Professionals exposed to pulse radiation

ALARM

PULSE

RADIATION

MEASUREMENT





CONTINUOUS AND PULSE X-RAY AND GAMMA RADIATION PERSONAL DOSIMETER

610B-01

SPECIFICATIONS

SPECIFICATIONS	
Detector	Geiger-Mueller tube
Dose equivalent rate (DER) indication range	0.01 μSv/h - 12.0 Sv/h (1 Rem/h - 1200 Rem/h)
DER measurement range	0.1 μSv/h - 10.0 Sv/h (10 Rem/h - 1000 Rem/h)
DER threshold range (in all measurement range)	Two threshold levels
Dose equivalent (DE) indication range	0.001 μSv - 24.0 Sv (0.1 Rem - 2400 Rem)
DE measurement range: - continuous photon radiation (current) - pulsed photon radiation (pulse duration not less than 1 ms)	0.05 μSv - 20.0 Sv (5 Rem - 2000 Rem) 10 μSv - 20.0 Sv (1000 Rem - 2000 Rem)
DE threshold range (in all measurement range)	Two threshold levels Default settings for dose: - threshold 1: 5 mSv (500 mRem), - threshold 2: 10 mSv (1000 mRem)
Minimum pulse duration of X-ray and gamma radiation	1 ms at multiple exposure (more than 10 pulses) 10 ms at single exposure
Accuracy of DER measurement	±(10 + 0.0015/H+0.0015H) %, where H - DER value in mSv/h
Accuracy of DE measurement in the range 0.05 µSv - 20.0 Sv	±20%
Energy range	20 keV - 10 MeV
Energy response relative to 0.662 MeV (¹³⁷ Cs) in the DER and DE measurement mode, not more than	- 60% 20 keV - 33 keV; - 40% 33 keV - 48 keV; ±30% 48 keV - 3 MeV; ±50% 3 MeV - 10 MeV.
Communications	- USB interface - ISO15693 interface for PM1610B-01
Features	- PC communication via USB - Audio alarm - Visual alarm - Vibration alarm - Holder with clip
Automatic data logging	7500 data points
Power supply	Battery type LR03/AAA
Operating time on new battery in normal conditions	no less than 20 days
Low battery (partial and critical)	Indication on LCD
Operating conditions: - temperature range - pressure Case Protection Class	-20 - +50°C 84 - 106.7 kPa IP65
Dimensions	71x59x20 mm
Weight	90 g

Design and specifications of the device can be changed without further notice.

(€ ISO 9001

Polimaster Inc 2200 Clarendon Blvd., Ste.1204 Arlington, VA 22201, USA Phone: +1 703 525 5075 Fax: +1 703 525 5079

North and South America

info@polimaster.us

Europe

Polimaster Europe UAB Ezero Str. 4, LT-13264 Didziasalis, Vilnius region, Republic of Lithuania Phone: +370 5 210 2323 Fax: +370 5 210 2322 polimaster@polimaster.lt

Asia, Africa, Australia and Oceania Polimaster Ltd.

112, Bogdanovich St.,
Minsk, 220040, Republic of Belarus
Phone: +375 17 396 3675
+375 17 268 6819 +375 17 260 2356

Japan Polimaster Pacific K. K. 3rd Floor #32 Arai Building, 3-9-14 Kudan-Minami, Chiyoda-ku Tokyo, Japan Phone: +81 03 6272 4280 Fax: +81 03 6272 4290

pacific@polimaster.jp